

XTRUE Dimensional Comparison

Frame	Manufacturer	Product	Bolt Circle mm	Shaft Dia. mm	Shaft Length mm	Pilot Dia. mm	Round	Tapped Output Face	Thread
40 mm	Micron	XT40	34	10	26	26	Y	Y	M4
	Alpha	LP50	44	12	24,5	35	Y	Y	M4
	Alpha	Alphira 040	34	10	26	26	Y	Y	M4
	Neugart	PLE-040	34	10	26	26	Y	Y	M4
	Bayside	PV40-TN	34	10	26	26	Y	Y	M4
	Bayside	PV40-TA	44	12	25	35	Y	Y	M4
	Apex	PE50	44	12	24,5	35	Y	Y	M4
	Stober	PE201	44	12	24,5	35	Y	Y	M4
	Gam	EPLW-50	44	12	24,5	35	Y	Y	M4
60 mm	Micron	XT60	52	14	35	40	Y	Y	M5
	Alpha	LP70	62	16	36	52	Y	Y	M5
	Alpha	Alphira 060	52	14	35	40	Y	Y	M5
	Neugart	PLE-060	52	14	35	40	Y	Y	M5
	Bayside	PV60-TN	52	14	35	40	Y	Y	M5
	Bayside	PV60-TA	60	16	36	52	Y	Y	M5
	Apex	PE70	62	16	36	52	Y	Y	M5
	Stober	PE301	62	16	36	52	Y	Y	M5
	Gam	EPLW-64	52	14	39	40	Y	Y	M5
80 mm	Micron	XT80	70	20	40	60	Y	Y	M6
	Alpha	LP90	80	22	46	68	Y	Y	M6
	Alpha	Alphira 080	70	20	40	60	Y	Y	M6
	Neugart	PLE-080	70	20	40	60	Y	Y	M6
	Bayside	PV90-TN	70	20	40	60	Y	Y	M6
	Bayside	PV90-TA	80	22	46	68	Y	Y	M6
	Apex	PE90	80	22	46	68	Y	Y	M6
	Stober	PE401	80	22	46	68	Y	Y	M6
	Gam	EPLW-84	70	20	54	55	Y	Y	M6
120 mm	Micron	XT120	100	25	55	80	Y	Y	M10
	Alpha	LP120	108	32	70	90	Y	Y	M8
	Alpha	Alphira 115	100	25	55	80	Y	Y	M10
	Neugart	PLE-120	100	25	55	80	Y	Y	M10
	Apex	PE120	108	32	70	90	Y	Y	M8
	Stober	PE501	108	32	70	90	Y	Y	M8
	Gam	EPL-W118	100	25	61	80	Y	Y	M8
160 mm	Micron	XT160	145	40	87	130	Y	Y	M12
	Alpha	LP155	140	40	97	120	Y	Y	M10
	Neugart	PLE-160	145	40	87	130	Y	Y	M12
	Apex	PE155	140	40	97	120	Y	Y	M10
	Gam	EPL-W150	130	30	81	110	Y	Y	M10

